

STEICO *multi tape F*

High performance tape with special foil



High performance tape with special foil for internal and external use

- Solvent-free
- Can be processed from -10 °C, temperature resistant between -40° and +100°C
- High UV and ageing resistance
- High moisture resistance/ rainproof
- With split release paper for the simple formation of e.g. corner bonds

Application area



- Joint and connection bonding of STEICO wood fibre boards in combination with STEICO *multi primer*
- Joint and connection bonding in the STEICO membrane system
- Connection bonding for STEICO *fix* and STEICO *tri* sub-window sills

Technical data

Temperature resistance [°C]	-40 / +100
Processing temperature [°C]	> -10; The surface must be dry and free of ice
Minimum roof pitch [°]	10
Adhesive	Acrylic dispersion, solvent-free
Adhesive backing	UV-stabilised special film with polyester lattice, single-sided adhesion
Colour	Grey
Thickness (without release paper) [mm] (approx.)	0,3
UV resistance [months]	12
Peeling strength	fulfilled according to DIN 4108/11
Peel strength after ageing	fulfilled according to DIN 4108/11

Forms of delivery

Length [mm]	Width [mm]	Release liner perforation [mm]	Number/pack. [pcs.]
25000	60	-	10

Roll with slit release paper

Length [mm]	Width [mm]	Release liner perforation [mm]	Number/pack. [pcs.]
25000	60	20/40	10
25000	100	50/50	6
25000	150	75/75	4



High performance tape with special foil

Weight and packing

Length [mm]	Width [mm]	Weight/m ² [kg]	Weight/pcs. [kg]	Weight/pack. [kg]	Packaging/pack. Paper/cardboard (approx.) [kg]
25000	60	0.65	0.7	7.60	0.60

Roll with slit release paper

Length [mm]	Width [mm]	Weight/m ² [kg]	Weight/pcs. [kg]	Weight/pack. [kg]	Packaging/pack. Paper/cardboard (approx.) [kg]
25000	60	0.65	0.7	7.70	0.60
25000	100	1.08	1.1	7.70	0.60
25000	150	1.62	1.8	7.70	0.60

Notes

Storage

- Store in a cool and dry place at +5 to +25 °C
- Protect from heat, cold and UV radiation

Ingredients

- Acrylic dispersion (solvent-free), special film, polyester scrim

Disposal

- dispose with normal construction waste, observe applicable legal guidelines

Cutting

- Sharp knife or other suitable cutting tool

Installation

Application in the STEICO membrane system

- Substrates must be stable, dry and free of dust and grease
- Align STEICO*multi tape F* in the middle, remove the release paper step by step, and rub the adhesive tape vigorously in the process
- Slit release paper facilitates the bonding of corners, as liners can be removed in turn as required
- The adhesive tape must be applied without creases
- If tensile forces occur, the substrate must also be mechanically fastened
- Bonds must not be in standing water. Bonding in sauna and swimming pool construction is also not permitted

Installation on STEICO wood fibre boards

- Pre-treat STEICO wood fibre boards in the bonding area with STEICO*multi primer*
- After sufficient flash-off time (if primer is transparent), apply STEICO*multi tape F*, remove release paper and rub on
- The bonding area per butt joint side must be at least 50 mm.
- To improve adhesion, additional pressing with a paint roller or roofing roller is recommended

STEICO *multi tape F*

High performance tape with special foil

Certificates and quality management



☰ Caption

other abbreviations

- pal.** Pallet
- T&G** Tongue and Groove
- pac.** Packaging
- approx.** Approximately

Responsible for content

STEICO UK Ltd
Unit 3 Eden Brae Business Park, Dunstable Road
Caddington LU1 4FF
Great Britain
Web: www.steico.com
Mail: info@steico.com

Version: 1

Date: 2025-05-12

The contents of this document have been prepared with the utmost care. However, applicable regulations can change. STEICO accepts no liability for the accuracy, completeness, or current applicability of the content. Application areas may vary in the detailing. Always verify the suitability of our products for the specific intended use.

This document is valid in the following countries:

United Kingdom, Republic of Ireland

The currently valid version can be found at: www.steico.com/tds_stemicomulti_tapef_gbr-irl_en